



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M8X40

Article number	24662.080.040
Brand	-
UBB	951353646858
UNSPSC	31161504
EAN	8715492640482
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	16
Full thread if $L \leq$	40
k	6
L (mm)	40
No. cross recess	4
P	1.25

Technical Drawing

