



Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M2,5X4

Article number	24665.025.004
Brand	-
UBB	950353904341
UNSPSC	31161504
EAN	8715492640550
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	4 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	5
Full thread if L ≤	20
k	2
L (mm)	4
No. cross recess	1
P	0.45

Technical Drawing

