



Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M2,5X10

Article number	24665.025.010
Brand	-
UBB	950353904754
UNSPSC	31161504
EAN	8715492640598
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	10 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	5
Full thread if $L \leq$	20
k	2
L (mm)	10
No. cross recess	1
P	0.45

Technical Drawing

