



Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M3X8

Article number	24665.030.008
Brand	-
UBB	950353905173
UNSPSC	31161504
EAN	8715492640666
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if $L \leq$	20
k	2.4
L (mm)	8
No. cross recess	1
P	0.5

Technical Drawing

