



## Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M4X12

Article number	24665.040.012
Brand	-
UBB	950353906247
UNSPSC	31161504
EAN	8715492640802
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M4
Length	12 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

DIN	7985
ISO	≈7045

### Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	8
Full thread if $L \leq$	25
k	3.1
L (mm)	12
No. cross recess	2
P	0.7

### Technical Drawing

