



Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M5X30

Article number	24665.050.030
Brand	-
UBB	950353907492
UNSPSC	31161504
EAN	8715492640963
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	30 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	10
Full thread if $L \leq$	28
k	3.8
L (mm)	30
No. cross recess	2
P	0.8

Technical Drawing

