

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M6X12



Article number	24665.060.012
Brand	-
UBB	950353908060
UNSPSC	31161504
EAN	8715492641045
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	12
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	7045-H
DIN	7985-H

Technical Specification

Thread length (min.)	28
d_k (max.)	12
Full thread if $L \leq$	35
k	4.6
No. cross recess	3
P	1

Technical Drawing

