

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M6X35



Article number 24665.060.035

Brand -

UBB 950353908557

UNSPSC 31161504

EAN 8715492641090

PKG. of 100 Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	35
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985-H
ISO	7045-H

Technical Specification

Thread length (min.)	28
d_k (max.)	12
Full thread if $L \leq$	35
k	4.6
No. cross recess	3
P	1

Technical Drawing

