



Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M6X40

Article number	24665.060.040
Brand	-
UBB	950353908631
UNSPSC	31161504
EAN	8715492641106
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	40 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	12
Full thread if $L \leq$	35
k	4.6
L (mm)	40
No. cross recess	3
P	1

Technical Drawing

