



## Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 M6X70

Article number	24665.060.070
Brand	-
UBB	500621768349
UNSPSC	31161504
EAN	8715494509169
PKG. of 100	Full Box Only

### Technical Parameters

Diameter	M6
Length	70 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

ISO	≈7045
DIN	7985

### Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	12
Full thread if L ≤	35
k	4.6
L (mm)	70
No. cross recess	3
P	1

### Technical Drawing

