



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 large pack M3X30

Article number	24670.030.030
Brand	-
UBB	500645207811
UNSPSC	31161504
EAN	8717077071414
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	large pack

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	30
No. cross recess	1
P	0.5

Technical Drawing

