



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 large pack M4X5

Article number	24670.040.005
Brand	-
UBB	500645208231
UNSPSC	31161504
EAN	8717077071452
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M4
Length	5 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	large pack

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	5
No. cross recess	2
P	0.7

Technical Drawing

