



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M3X5

Article number	24671.030.005
Brand	-
UBB	951353504602
UNSPSC	31161504
EAN	8715492641977
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	5 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

Standards

DIN	965
NF	≈E25-119-1
ISO	≈7046-1

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65

Technical Drawing

L (mm)	5
No. cross recess	1
P	0.5

