



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M3X12

Article number	24671.030.012
Brand	-
UBB	951353505021
UNSPSC	31161504
EAN	8715492642011
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	12 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65

Technical Drawing

L (mm) 12

No. cross recess 1

P 0.5

