



## Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M3X30

Article number 24671.030.030

Brand -

UBB 500621768596

UNSPSC 31161504

EAN 8715494509183

PKG. of 200 Full Box Only

### Technical Parameters

Diameter	M3
Length	30 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

### Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

### Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65

### Technical Drawing

L (mm)	30
No. cross recess	1
P	0.5

