



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M3X40

Article number	24671.030.040
Brand	-
UBB	500621768679
UNSPSC	31161504
EAN	8715494509190
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	40 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65

Technical Drawing

L (mm) 40

No. cross recess 1

P 0.5

