

Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M3X40



Article number	24671.030.040
Brand	-
UBB	500621768679
UNSPSC	31161504
EAN	8715494509190
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	40
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	965 A-H
NF	E25-119-1
ISO	7046-1-H

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
No. cross recess	1
P	0.50

Technical Drawing

