

## Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M4X10



Article number	24671.040.010
Brand	-
UBB	951353505518
UNSPSC	31161504
EAN	8715492642066
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	10
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

ISO	7046-1-H
DIN	965 A-H
NF	E25-119-1

### Technical Specification

Thread length (min.)	22
$d_k$ (max.)	7.5
Full thread if $L \leq$	25
$k$ (max.)	2.2
No. cross recess	2
P	0.70

### Technical Drawing

