



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M4X12

Article number 24671.040.012

Brand -

UBB 951353505690

UNSPSC 31161504

EAN 8715492642073

PKG. of 200 Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if L ≤	25
k (max.)	2.2

Technical Drawing

L (mm) 12

No. cross recess 2

P 0.7

