



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M5X16

Article number	24671.050.016
Brand	-
UBB	951353506433
UNSPSC	31161504
EAN	8715492642165
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	16 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5

Technical Drawing

L (mm) 16

No. cross recess 2

P 0.8

