



## Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M5X50

Article number	24671.050.050
Brand	-
UBB	951353507001
UNSPSC	31161504
EAN	8715492642226
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M5
Length	50 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

### Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

### Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5

### Technical Drawing

L (mm) 50

No. cross recess 2

P 0.8

