



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Steel Zinc plated 4.8 M1,6X4

Article number	24672.016.004
Brand	-
UBB	500654333649
UNSPSC	31161504
EAN	8712423010505
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.6
Length	4 mm
Class	4.8
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M1.6
Thread length (min.)	15
dk (max.)	3
Full thread if $L \leq$	16
k (max.)	0.96
L (mm)	4
No. cross recess	0
P	0.35

Technical Drawing

