



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Steel Zinc plated 4.8 M2X6

Article number	24672.020.006
Brand	-
UBB	500654334142
UNSPSC	31161504
EAN	8712423010550
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	6 mm
Class	4.8
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if L ≤	18
k (max.)	1.2
L (mm)	6
No. cross recess	1
P	0.4

Technical Drawing

