



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Steel Zinc plated 4.8 large pack M6X25

Article number	24690.060.025
Brand	-
UBB	950353170232
UNSPSC	31161504
EAN	8715492643292
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M6
Length	25 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	large pack

Standards

ISO	≈7047
DIN	966
NF	≈E25-120

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	25
No. cross recess	3
P	1

Technical Drawing

