



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Steel Zinc plated 4.8 M3X10

Article number	24691.030.010
Brand	-
UBB	951353508744
UNSPSC	31161504
EAN	8715492643445
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	966
ISO	≈7047
NF	≈E25-120

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	10
No. cross recess	1
P	0.5

Technical Drawing

