



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Steel Zinc plated 4.8 M4X6

Article number	24691.040.006
Brand	-
UBB	951353509163
UNSPSC	31161504
EAN	8715492643483
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	6 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	966
NF	≈E25-120
ISO	≈7047

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	6
No. cross recess	2
P	0.7

Technical Drawing

