



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Steel Zinc plated 4.8 M4X8

Article number	24691.040.008
Brand	-
UBB	951353509247
UNSPSC	31161504
EAN	8715492643490
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	8 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	966
ISO	≈7047
NF	≈E25-120

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	8
No. cross recess	2
P	0.7

Technical Drawing

