



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Steel Zinc plated 4.8 M4X12

Article number	24691.040.012
Brand	-
UBB	951353509403
UNSPSC	31161504
EAN	8715492643513
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	966
NF	≈E25-120
ISO	≈7047

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	12
No. cross recess	2
P	0.7

Technical Drawing

