



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Steel Zinc plated 4.8 M5X20

Article number	24691.050.020
Brand	-
UBB	951353510542
UNSPSC	31161504
EAN	8715492643612
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	20 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-120
ISO	≈7047
DIN	966

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	20
No. cross recess	2
P	0.8

Technical Drawing

