

Cross recessed raised countersunk head screw Pozidriv DIN 966 Steel Zinc plated 4.8 M3X10



Article number 24692.030.010

Brand -

UBB 950353749746

UNSPSC 31161504

EAN 8715492643834

PKG. of 2000 Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	10
Class	4.8
Driving features	Pozidriv
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7047
DIN	966
NF	≈E25-120

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
$f \approx$	0.75
Full thread if $L \leq$	22
k (max.)	1.65
No. cross recess	1
P	0.50

Technical Drawing

