



Cross recessed raised countersunk head screw Pozidriv DIN 966 A-Z Steel Zinc plated 4.8 M3X16

Article number	24692.030.016
Brand	-
UBB	950353963578
UNSPSC	31161504
EAN	8715492643858
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M3
Length	16 mm
Class	4.8
Driving features	Pozidriv
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7047
DIN	966
NF	≈E25-120

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	16
No. cross recess	1
P	0.5

Technical Drawing

