

## Cross recessed raised countersunk head screw Pozidriv DIN 966 A-Z Steel Zinc plated 4.8 M4X20



Article number 24692.040.020

Brand -

UBB 950353963651

UNSPSC 31161504

EAN 8715492643919

PKG. of 1000 Full Box Only

### Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	20
Class	4.8
Driving features	Pozidriv
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

NF	E25-120
DIN	966 A-Z
ISO	7047-Z

### Technical Specification

Thread length (min.)	22
$d_k$ (max.)	7.5
$f \approx$	1
Full thread if $L \leq$	25
$k$ (max.)	2.2
No. cross recess	2
P	0.70

### Technical Drawing

