



Cross recessed raised countersunk head screw Pozidriv DIN 966 A-Z Steel Zinc plated 4.8 M8X20

Article number	24692.080.020
Brand	-
UBB	951353638939
UNSPSC	31161504
EAN	8715492644107
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Length	20 mm
Class	4.8
Driving features	Pozidriv
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-120
ISO	≈7047
DIN	966

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
f ≈	2
Full thread if L ≤	40
k (max.)	4
L (mm)	20
No. cross recess	4
P	1.25

Technical Drawing

