



Cross recessed raised countersunk head screw Pozidriv DIN 966 A-Z Steel Zinc plated 4.8 M8X25

Article number	24692.080.025
Brand	-
UBB	951353639010
UNSPSC	31161504
EAN	8715492644114
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Length	25 mm
Class	4.8
Driving features	Pozidriv
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	966
ISO	≈7047
NF	≈E25-120

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
f ≈	2
Full thread if L ≤	40
k (max.)	4
L (mm)	25
No. cross recess	4
P	1.25

Technical Drawing

