

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated yellow passivated 4.8 M3X10

Article number	24800.030.010
Brand	-
UBB	950353171719
UNSPSC	31161504
EAN	8715492644343
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if $L \leq$	20
k	2.4
L (mm)	10
No. cross recess	1
P	0.5

Technical Drawing

