

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M3X8

| | |
|----------------|---------------|
| Article number | 24810.030.008 |
| Brand | - |
| UBB | 950353174945 |
| UNSPSC | 31161504 |
| EAN | 8715492644817 |
| PKG. of 200 | Full Box Only |

Technical Parameters

| | |
|-------------------|------------------------------|
| Diameter | M3 |
| Length | 8 mm |
| Class | 4.8 |
| Driving features | Phillips |
| Head shape | Raised cheese head |
| Material | Steel |
| Surface treatment | Zinc plated black passivated |
| Thread | Metric thread |

Standards

| | |
|-----|-------|
| ISO | ≈7045 |
| DIN | 7985 |

Technical Specification

| | |
|-------------------------|-----|
| d-D | M3 |
| Thread length (min.) | 19 |
| dk (max.) | 6 |
| Full thread if $L \leq$ | 20 |
| k | 2.4 |
| L (mm) | 8 |
| No. cross recess | 1 |
| P | 0.5 |

Technical Drawing

