

## Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M3X10

Article number 24810.030.010

Brand -

UBB 950353175025

UNSPSC 31161504

EAN 8715492644824

PKG. of 200 Full Box Only

### Technical Parameters

Diameter	M3
Length	10 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

### Standards

DIN	7985
ISO	≈7045

### Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if $L \leq$	20
k	2.4
L (mm)	10
No. cross recess	1
P	0.5

### Technical Drawing

