

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M3X20

Article number	24810.030.020
Brand	-
UBB	950353175363
UNSPSC	31161504
EAN	8715492644855
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if $L \leq$	20
k	2.4
L (mm)	20
No. cross recess	1
P	0.5

Technical Drawing

