

## Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M5X30

Article number	24810.050.030
Brand	-
UBB	950353875624
UNSPSC	31161504
EAN	8715492645067
PKG. of 100	Full Box Only

### Technical Parameters

Diameter	M5
Length	30 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

### Standards

ISO	≈7045
DIN	7985

### Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	10
Full thread if $L \leq$	28
k	3.8
L (mm)	30
No. cross recess	2
P	0.8

### Technical Drawing

