

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M6X10

Article number	24810.060.010
Brand	-
UBB	950353876200
UNSPSC	31161504
EAN	8715492645128
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	10 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	12
Full thread if $L \leq$	35
k	4.6
L (mm)	10
No. cross recess	3
P	1

Technical Drawing

