

## Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M6X10



Article number	24810.060.010
Brand	-
UBB	950353876200
UNSPSC	31161504
EAN	8715492645128
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	10
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

### Standards

ISO	7045-H
DIN	7985-H

### Technical Specification

Thread length (min.)	28
$d_k$ (max.)	12
Full thread if $L \leq$	35
k	4.6
No. cross recess	3
P	1

### Technical Drawing

