

## Cross recessed raised cheese head screw DIN 7985-H Steel Zinc plated with thick Cr(III) passivation 4.8 M3X12

Article number	24811.030.012
Brand	-
UBB	500649016929
UNSPSC	31161504
EAN	8717077250116
PKG. of 2000	Full Box Only

### Technical Parameters

Diameter	M3
Length	12 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

### Standards

DIN	7985
ISO	≈7045

### Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if L ≤	20
k	2.4
L (mm)	12
No. cross recess	1
P	0.5

### Technical Drawing

