



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated black passivated 4.8 M3X30

Article number	24840.030.030
Brand	-
UBB	950353177344
UNSPSC	31161504
EAN	8715492645425
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	30
No. cross recess	1
P	0.5

Technical Drawing

