



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated black passivated 4.8 M4X12

Article number	24840.040.012
Brand	-
UBB	950353177674
UNSPSC	31161504
EAN	8715492645463
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	12
No. cross recess	2
P	0.7

Technical Drawing

