



Slotted raised countersunk head wood screw DIN 95 Steel Zinc plated 2X20MM

Article number	25100.020.020
Brand	-
UBB	500649353777
UNSPSC	31161508
EAN	8717077266353
PKG. of 500	Full Box Only

Technical Parameters

Diameter	2 mm
Length	20 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Info	Wood screw thread acc. to DIN 7998.

Standards

NF	E25-605
DIN	95
NEN	2252

Technical Specification

D (mm)	2
dk	3.8
ds	2
f ≈	0.5
k (max.)	1.2
L (mm)	20
n	0.5

Technical Drawing

