



Slotted raised countersunk head tapping screw DIN 7973 C Steel Nickel plated ST3,5X13MM

Article number	26040.035.013
Brand	-
UBB	950352051946
UNSPSC	31161507
EAN	8715492651372
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	13 mm
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ISO	1483 C
DIN	7973 C
NF	E25-661 C
BS	4174

Technical Specification

D (mm)	3.5
dk	6.8
f ≈	1.2
k ≈	2.1
L (mm)	13
n	1
P	1.3

Technical Drawing

