

## Slotted raised countersunk head tapping screw DIN 7973 C Steel Nickel plated ST4,2X25MM



Article No.	26040.042.025
Brand	-
UBB	950352053686
UNSPSC	31161507
EAN	8715492651556
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (mm)	4.2
Length (L) (mm)	25
Driving features	Slotted
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

### Standards

BS	4174
DIN	7973 C
NF	E25-661 C
ISO	1483 C

### Technical Specification

$d_k$	8.1
$f \approx$	1.4
$k \approx$	2.5
$n$	1.2
$P$	1.40

### Technical Drawing

