

Cross recessed pan head tapping screw Phillips DIN 7981 C-H Steel Nickel plated ST3,5X6,5MM



Article No.	26200.035.006
Brand	-
UBB	950352064998
UNSPSC	31161507
EAN	8715492652850
PKG. of 200	Full Box Only

Technical Parameters

Diameter (mm)	3.5
Length (L) (mm)	6.5
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread

Info

Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Standards

ISO	7049 C-H
ASME	B18.6.4
NF	E25-658
DIN	7981 C-H

Technical Specification

d_k	6.9
k	2.6
No. cross recess	2
P	1.30

Technical Drawing

