



Cross recessed pan head tapping screw Phillips DIN 7981 C-H Steel Nickel plated ST4,8X25MM

Article number	26200.048.025
Brand	-
UBB	950352067215
UNSPSC	31161507
EAN	8715492653086
PKG. of 200	Full Box Only

Technical Parameters

Diameter	4.8 mm
Length	25 mm
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	7049 CH
DIN	7981 CH
ASME	B18.6.4
NF	E25-658

Technical Specification

D (mm)	4.8
dk	9.5
k	3.55
L (mm)	25
No. cross recess	2
P	1.6

Technical Drawing

