



Cross recessed pan head tapping screw with flat end Phillips DIN 7981 F-H Steel Nickel plated ST2,2X4,5MM

Article number	26300.022.004
Brand	-
UBB	950352082487
UNSPSC	31161507
EAN	8715492654205
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	2.2 mm
Length	4.5 mm
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread

Standards

DIN	7981 F
ASME	≈B18.6.5M-B
ISO	≈7049 F
BS	≈4174-B
NF	≈E25-658 F

Technical Specification

D (mm)	2.2
dk (max.)	4.2
k	1.8
L (mm)	4.5
No. cross recess	1
P	0.8

Technical Drawing

